




Pipe swaging machine complete



Order data

Order number	820900
GTIN	4004625260135
Item class	86B

Description

Version:

Cast steel base with 2 clamping blocks, 5 flare inserts (4.75 – 10 mm) and 1 pressure plate 90°. The machine can be clamped in any normal vice.

Clamping blocks for pipe Ø 4.75; 5; 6; 8; 9 and 10 mm. One face flat for 180° flares; one face countersunk for 90° flares.

Flare inserts for pipe Ø 4.75-5; 6; 8; 9 and 10 mm for flare shapes F and E. **Pressure plate 90°** for flare shapes D and E.

Application:

For standard double flares (DIN 74234) on brake lines and coolant lines etc., for hydraulics and pneumatics. For seamless drawn steel pipes, as well as double-walled rolled pipes (Bundy pipes).

Suitable for :

Flares D-E-F to DIN 74234.

Technical description

Type of product	Tube flaring tool
-----------------	-------------------

Accessories

Jaw anvil Type 1652	820950 1652
---------------------	-------------

Pair of clamping blocks Type M	820970 M
Swaging insert metric Type 8	820930 8
Swaging insert metric Type 6	820930 6
Swaging insert metric Type 10	820930 10
Swaging insert metric Type 4,75/5	820930 4,75/5
Swaging insert metric Type 9	820930 9