

**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Cup brush Steel wire 0.35 mm, Brush Ø D1: 100mm****Order data**

Order number	573000 100
GTIN	4017359032374
Item class	57L

**Description****Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

With **M14 internal thread**. With **M14 internal thread**.

**Application:**

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

**Technical description**

maximum speed	8500 min <sup>-1</sup>
Length of brush section H <sub>1</sub>	30 mm
Bristle thickness	0.35 mm
Brush Ø D <sub>1</sub>	100 mm
Thread M	M14
Brush material	Steel wire
Type of product	Cup brush

