


LESSMANN[®]
THE GERMAN BRUSH COMPANY**Wheel brush with shank micro-abrasive SiC 320 grit, Brush Ø D1× bristle width L1: 50X10mm****Order data**

Order number	574450 50X10
GTIN	4017359138298
Item class	57L

Description**Version:**

Abrasive nylon strands with silicon carbide, crimped into steel sleeve; **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

Wet and dry fine rubbing down of aluminium, steel, stainless steel and plastics. Maximum operating temperature 80 °C.

Technical description

Grit	320
Length of brush section H ₁	12 mm
recommended speed	6000 min ⁻¹
Brush Ø D ₁	50 mm
maximum speed	15000 min ⁻¹
Shank Ø D _s	6 mm

Grinding medium code	SiC
Type of product	Wheel brush