



## Water-tight case "Explorer", Type: 4820



### Order data

Order number	692930 4820
GTIN	8024482008684
Item class	64A

### Description

**Version:**

Extremely sturdy tool case of impact resistant plastic, filled with pre-shaped chequer foam. Lockable with padlock No. 085830 – 085875. Thick walls throughout for high stability. Pressure-tight and resistant to chemicals. Temperature-resistant from –33 °C to 90 °C. Heavenly Delight versions with a weight saving of approx. 30% and increased strength compared to previous models.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

For protection, packaging, and transport of delicate parts and devices.

**Note:**

Many other case sizes, fittings variants, and accessories available on request.

### Technical description

External dimension height	230 mm
Internal dimension height	205 mm

External dimension width	435 mm
maximum loading	24.7 kg
Weight	4.2 kg
External dimension length	520 mm
Number of catches	2
Internal dimension width	370 mm
Internal dimension length	480 mm
Volume	35.5 l
IP Index of Protection	IP 67
Characteristics case	impact resistant
Characteristics case	stackable
Characteristics case	suitable for air travel
Type of product	Tool transport system