

Garant**Torque wrench base unit without plug-in head, maximum torque: 25N·m****Order data**

Order number	656055 25
GTIN	4045197302250
Item class	61E

Description**Version:**

Handy and very compact one-armed torque wrench, adjustable by scale and self-triggering. Extremely high repeat accuracy, since high quality materials are used throughout. Wearing parts, such as compression springs, are specially pre-treated and sorted. Reversible ratchet for left-hand and right-hand tightening.

Acoustic and perceptible "click effect" ensures particularly easy use and accurate setting of the desired torque.

Basic tool with **square plug-in socket** (without plug-in head). Suitable spare jaws No. 657582 - 657950.

Units of measure: Nm

Function:

The wrench triggers giving a "signal" (clearly audible acoustic tone and noticeable vibration) and afterwards is immediately ready for use again.

Application:

For medium to larger batch productions.

Standard:

Geprüft nach DIN EN ISO 6789.

Accuracy:

Of the displayed value **only for right-hand tightening:** $\pm 3 \%$

Cutting dataa:**Legend for drawing and formula:**

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Note:

Calibration is only possible for right-hand tightening.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Display	analogue
maximum torque	25 Nm
Socket for plug-in head	9×12 mm
Torque measuring accuracy	±3 %
Direction of tightening	For right and left-hand tightening
Exchangeable tool	Plug-in head
Scale graduation, 1 graduation =	0.25 Nm
Torque range	2.5 - 25 Nm
Lever length including factory calibration reference dimension [I ₃]	185.5 mm
Standard	DIN EN ISO 6789
Feedback	triggering
Trigger principle	mechanical short-travel release
Overall length L	225 mm
Setting the trigger value	with adjustment scale
Adjusted reference dimension on the torque wrench [I ₂]	17.5 mm
Lever length without plug-in head [I ₁]	168 mm
Connection format	for plug-in heads (rectangular socket)
Measurement process	Torque
Reversible reading	Nm
Adjustable trigger value	adjustable
Calibration	O1
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk

Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque Wrench

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/656055-25>