



Burr set 8 pieces, Z steel – coarse, Carbide



Order data

Order number	547120
GTIN	
Item class	52D

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

Sets of burrs in the most popular shapes and sizes. Shank Ø 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Supplied with:

1 pc. each No. 540740 size A0616; A1020; A1225; C1225; D1009; G0820; F1225; L1020.

Technical description

Tooth type abbreviation	Z steel
Toothing grit designation	coarse
Tool material	Carbide
Shank Ø	6 mm

Number of burrs	8
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		