



## Water-tight case "Explorer", Type: 7630



### Order data

Order number	692930 7630
GTIN	8024482008806
Item class	64A

### Description

**Version:**

Extremely sturdy tool case of impact resistant plastic, filled with pre-shaped chequer foam. Lockable with padlock No. 085830 – 085875. Thick walls throughout for high stability. Pressure-tight and resistant to chemicals. Temperature-resistant from –33 °C to 90 °C.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

For protection, packaging, and transport of delicate parts and devices.

**Note:**

Many other case sizes, fittings variants, and accessories available on request.

### Technical description

External dimension width	560 mm
Internal dimension width	485 mm
Volume	113.1 l

Number of catches	7
Weight	16.4 kg
Internal dimension length	765 mm
External dimension height	355 mm
External dimension length	860 mm
Number of side handles	2
maximum loading	81.8 kg
Number of wheels	2
Internal dimension height	305 mm
IP Index of Protection	IP 67
Characteristics case	impact resistant
Characteristics case	stackable
Characteristics case	suitable for air travel
Type of product	Tool transport system