



## Torque wrench with reversible ratchet, maximum torque: 60N·m



### Order data

Order number	656500 60
GTIN	4000896025022
Item class	630

### Description

#### Version:

Handy and very compact single-arm torque wrench, adjustable by scale and self-triggering. Extremely high repeat accuracy, since high quality materials are used throughout. Wearing parts, such as compression springs, are specially pre-treated and sorted. Reversible ratchet for left-hand and right-hand tightening.

With built-in **reversible ratchet – for left and right hand tightening.**

**Units of measure:** Nm With HiPer fine tooth reversible ratchet (90 teeth, 4° actuation angle).

#### Function:

The wrench triggers giving a "signal" (clearly audible acoustic tone and noticeable vibration) and afterwards is immediately ready for use again.

#### Application:

For medium to larger batch productions.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Accuracy:

Of the displayed value **only for right-hand tightening: ±2 %.**

#### Cutting dataa:

#### Legend for drawing and formula:

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

L = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

**Note:**

Calibration is only possible for right-hand tightening.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

---

**Technical description**

Weight	1000 g
Display	analogue
Square drive	3/8 in
maximum torque	60 Nm
Torque measuring accuracy	±2 %
Direction of tightening	For right and left-hand tightening
Scale graduation, 1 graduation =	0.5 Nm
Torque range	5 - 60 Nm
Adjustable trigger value	adjustable
Reversible reading	Nm
Connection format	Push-through square drive (ratchet)
Standard	DIN EN ISO 6789
Feedback	triggering
Overall length L	335 mm
Measurement process	Torque
Lever length including factory calibration reference dimension [l <sub>3</sub> ]	265 mm
Setting the trigger value	with adjustment scale
Trigger principle	mechanical short-travel release
Calibration	O1
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Release signalling	optisk

Measurement technology	mechanical
Type of product	Torque Wrench

**Services**

DAkkS calibrationTorque wrench maximum torque 1000 N·m	020020 1000
CalibrationTorque wrench maximum torque 400 N·m	020010 400