



Torque wrench QuickSelect with plug-in ratchet, maximum torque: 800N·m



Order data

Order number	657090 800
GTIN	2050002047105
Item class	63A

Description

Version:

Sturdy compact one-armed torque wrench, adjustable to scale and self-triggering. The accuracy is sustained for many thousands of operations, because high quality material is used for all wearing parts and the flexible rod is under load only briefly on each occasion. Body and handle are of sturdy square section. Scales adjustable. **Anti-clockwise tightening by reversing the plug-in tools. Units of measure:** Nm, lbfft.

With **plug-in ratchet with push-through square.**

Advantage:

- **Ergonomically shaped two-component handle, resistant to aggressive liquids such as fuel, Skydrol etc.**
- **The adjustment scale is placed behind a sight glass for protection against dirt and damage.**
- **Quick, precise, and reliable setting: Pull the setting knob, "Twist" to set the desired value and "Press" to save it. Setting knob moves easily since there is no spring pressure to be overcome.**

Function:

If the set value is reached while using the wrench, the wrench triggers giving a "signal" (acoustic and perceptible) and is then immediately ready for use again.

Application:

Since the set torque can be varied, it is ideal for repairs and short series production.

Standard:

Geprüft nach DIN EN ISO 6789.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

maximum torque	800 Nm
Weight	6800 g
Display	analogue
Square drive	3/4 in
Socket for plug-in head	22×28 mm
Torque measuring accuracy	±3 %
Direction of tightening	For right and left-hand tightening
Exchangeable tool	Plug-in head
Scale graduation, 1 graduation =	5 Nm
Torque range	160 - 800 Nm
Torque range	120 - 600 lbfft
Measurement process	Torque
Lever length without plug-in head [l_1]	1167 mm
Setting the trigger value	with adjustment scale
Trigger principle	mechanical short-travel release
Connection format	for plug-in heads (rectangular socket)
Lever length including factory calibration reference dimension [l_3]	1222 mm
Reversible reading	Nm
Reversible reading	lbfft
Adjustable trigger value	adjustable
Feedback	triggering
Adjusted reference dimension on the torque wrench [l_2]	55 mm

Standard	DIN EN ISO 6789
Calibration	O1
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Series	MANOSKOP® 730N
Type of product	Torque Wrench

Services

DAkkS calibrationTorque wrench maximum torque 1000 N·m	020020 1000
CalibrationTorque wrench maximum torque 1000 N·m	020010 1000

Accessories

Torque wrench QuickSelectwithout plug-in head maximum torque 800 N·m	657094 800
--	------------