



## Cordless hammer drill / driver, Manufacturer ID: GSB1215



### Order data

Order number	070104 GSB1215
GTIN	3165140727518
Item class	03B

### Description

#### Version:

**Bosch cordless drill / driver** for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP) protects the battery against overheating and deep discharge.**
- **Electronic Motor Protection (EMP) protects the motor against overloading.**
- **With motor brake and mechanical multi-stage torque shut-down.**
- **Handy belt clip (not 070104).**
- **Integral LED lamp, battery charge status display.**
- **Quick-release drill chuck.**

Sturdy and handy cordless drill / driver, only **1 kg** in weight.

#### Supplied with:

Supplied with 2x 12 V / 2.0 Ah Li-ion battery, charger and L-BOXX.

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB.

#### Note:

See No. 073851 ff. and 073866 ff for suitable spare batteries and chargers.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 12 V

Manufacturer's designation: GSB 12V-15

Motor design: Motor with brushes  
 Battery voltage: 12 V  
 Battery capacity: 2 A·h  
 maximum torque soft: 15 N·m  
 maximum torque hard: 30 N·m

## Technical description

suitable battery - supplier / battery type / voltage	Bosch 12 V
Battery voltage	12 V
maximum speed 2nd speed	1300 rpm
maximum speed 1st speed	0 - 380 rpm
maximum vibration to EN without hammer drill function	< 2.5 m/s <sup>2</sup>
Battery capacity	2 A·h
maximum torque soft	15 N·m
maximum twist drill size Ø in steel	10 mm
Motor design	Motor with brushes
Weight	1 kg
maximum twist drill size Ø in wood	19 mm
maximum vibration to EN with hammer drill function	10.5 m/s <sup>2</sup>
Packaging	Modular case (L-Boxx)
maximum torque hard	30 N·m
Manufacturer ID	GSB1215
Quick-clamping chuck range	1 - 10 mm
maximum twist drill size Ø in concrete	10 mm
Manufacturer's designation	GSB 12V-15
typical application	Medium
Number of rechargeable batteries contained	2
Battery type	Lithium-ion

## Accessories

Li-ion battery Battery type, battery voltage B12 V	073851 B12
Li-ion battery Battery type, battery voltage B12 V	073852 B12
Battery charger Manufacturer's designation AL1130CV	073866 AL1130CV