



Cordless hammer drill / driver, Type: 71132362

Order data

Order number	070100 71132362
GTIN	4014586887210
Item class	03F

Description

Version:

2-speed cordless impact drill driver with brushless motor.

- **Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.**
- **2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.**
- **With QuickIN all-metal drill chuck (120 Nm) with carbide-coated jaws and high clamping forces.**
- **Mechanical torque setting.**
- **FEIN SafetyCell technology. Protects the battery and the machine against overheating and deep discharge.**
- **Sturdy metal gearbox for long working life.**

Supplied with:

Supplied with 2 × 18 V / 2.5 Ah Li-ion battery, 1 × ALG 50 quick charger, 1 × QuickIN drill chuck (120 Nm), 1 × belt clip, 1 × bit garage, carrying case.

Note:

See No. 073835 ff. for suitable batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Manufacturer's designation: ASB 18 QC

Motor design: Brushless

Battery voltage: 18 V

Battery capacity: 2.5 A·h

maximum torque soft: 32 N·m

maximum torque hard: 60 N·m

Technical description

Type of product

