



Cordless circular saw, Type: M18FMCS



Order data

Order number	078207 M18FMCS
GTIN	4002395289288
Item class	03L

Description

Version:

Integral retainer for the hexagon L-wrench.

Handy and powerful 18 V / 5.0 Ah cordless circular metal saw for cutting pipes, profiles, threaded rods and cable ducts.

- **Brushless POWERSTATE™ motor for higher cutting speeds.**
- **REDLINK PLUS™ electronics with digital overload protection, for more power.**
- **Metal hook for simple and secure suspension of the unit.**
- **Cold cutting without burrs or sparks.**
- **Depth of cut setting, no tools required, for cuts 1 to 57 mm deep.**

Supplied with:

Supplied with charger, hexagon L-wrench, 34-tooth carbide saw blade and carrying case (HD box).

Note:

See from No. 073814 and No. 073839 for suitable spare batteries and starter kits. For a suitable circular saw blade see No. 078212 size 150X20T34.

Technical description

Saw blade Ø	150 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V

suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
Packaging	Modular case (HD=Heavy Duty)
Battery voltage	18 V
maximum cutting depth 90°	57 mm
maximum speed	3900 min ⁻¹
maximum vibration to EN	< 2.5 m/s ²
Weight	2.8 kg
Battery capacity	5 Ah
Saw blade bore Ø	20 mm
Manufacturer's designation	M18FMCS-502X
Version	Hand-held circular saw
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Saw

Accessories

Battery charger Type M1218FC	073840 M1218FC
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218C	073840 M1218C