



Angle grinder GWS, Type: 15-125CIEP



Order data

Order number	077109 15-125CIEP
GTIN	3165140861519
Item class	03C

Description

Version:

1500 W motor and **maximum protection function** due to additional **motor brake (Intelligent Brake System)** with up to 70 % shorter run-down time) and PROtection switch that can be actuated at various places, which switches the machine off immediately the trigger is released. With electronic speed control. Spindle thread M14×1.5.

Powerful angle grinder in a compact format.

- **Powerful motor with constant-speed electronics, soft start and start-up current limitation.**
- **Long working life, thanks to direct cooling and overload protection.**
- **High user protection due to vibration control. Additional handle, kick-back stop and restart inhibit.**

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Manufacturer's designation: GWS 15-125 CIEPX

Power consumption: 1500 W

Speed range: 2800 - 12000 min⁻¹

Connection thread: M14×1.5

maximum vibration to EN: 6 m/s²

maximum disc Ø: 125 mm

Technical description

maximum vibration to EN	6 m/s ²
-------------------------	--------------------

Restart block	yes
Manufacturer's designation	GWS 15-125 CIEPX
Special features	Very high user protection
Power consumption	1500 W
Soft start	yes
Weight	2.5 kg
maximum cutting depth	34 mm
Kick-back stop	yes
maximum disc Ø	125 mm
Speed range	2800 - 12000 min ⁻¹
Connection thread	M14×1.5
Power supply	Mains operated
Type of product	Angle grinder