

KÄRCHER**Wet and dry vacuum cleaner, Manufacturer's designation: NT30TEL****Order data**

Order number	078521 NT30TEL
GTIN	4054278046006
Item class	07C

Description**Version:**

Powerful all-purpose **wet and dry cleaners** with high suction power and compact design, hose storage, and accessory storage on the cleaner. **Automatic shut-down** when the maximum filling level is reached in the container.

- **Folded filter enables wet and dry suction without removing the filter.**
- **The Tact automatic filter cleaning system permits uninterrupted work in combination with low maintenance costs and long working life of the filter.**
- **The central rotary switch permits easy switching between the suction programs.**
- **The large top-mounted Eco flat fold filter permits immediate change from wet to dry suction without removing the filter.**
- **The central rotary switch permits easy switching between the suction programmes.**
- **With stepless speed control and anti-static system (earthing is maintained through to the extraction system attachment).**
- **Additionally with socket for connection of electrical equipment (up to maximum 2200 W). The automatic switch-on starts the suction when the electric tool is switched on. 15 second delayed switch-off.**
- **The new tool sleeve ensures an optimum connection for the electric tool. Adjustment of the suction force by the twist ring on the base body of the sleeve.**
- **The Tact automatic filter cleaning system permits uninterrupted work in combination with low maintenance costs and long working life of the filter.**

· **Robust 30-litre container with bumpers and metal castors.**

Supplied with:

Suction hose with elbow, metal suction tube 2x0.5 m, floor nozzle, and crevice nozzle, flat fold filter or paper filter bag.

Note:

Industrial vacuum cleaner No. 078522 for materials that are oily or contain oil.

Technical description

Width	370 mm
Vacuum	254 mbar
Operating noise	69 dB(A)
Filter cleaning	Tact automatic filter cleaning
Power consumption	1380 W
Suction hose length	4 m
Anti-static system	yes
Connection width	35 mm
Dust class – vacuum cleaner	L
Weight	14 kg
Air flow volume	74 l/s
Number of turbines	1
Cable length	7.5 m
Automatic switch-on	yes
Manufacturer's designation	NT 30/1 Tact Te L *
Container volume	30 l
Height	580 mm
Length	560 mm
Filter system	Eco flat fold filter
Special features	Robust container with bumper
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

Accessories

Filter bag set 5 pieces suitable for vacuum cleaner type NT30

072808 NT30

Flat fold filter suitable for vacuum cleaner type NT30

072809 NT30