

LESSMANN®
THE GERMAN BRUSH COMPANY**End brush Steel wire 0.30 mm, Type: 10X80****Order data**

Order number	574500 10X80
GTIN	4017359006931
Item class	57L

Description**Version:**

Waved special high quality wire, crimped into steel ferrule, **shank Ø 6 mm.**

Application:

For straight die grinders, on flexible drive machines and drills. For cleaning and deburring at inaccessible places.

Technical description

Length of brush section H ₁	20 mm
Clamp length L ₂	80 mm
Clamp Ø D ₂	10 mm
Brush Ø D ₁	12 mm
maximum speed	15000 min ⁻¹
Overall length L	120 mm
Type of product	End brush