

LESSMANN®
THE GERMAN BRUSH COMPANY

End brush Brass-coated steel wire 0.25 mm, Type: 22X22



Order data

Order number	574700 22X22
GTIN	4017359114773
Item class	57L

Description

Version:

Waved special high quality wire, crimped into steel ferrule, **shank Ø 6 mm**.

Application:

For straight die grinders, on flexible drive machines and drills. For cleaning and deburring at inaccessible places.

Brush Ø D₁: 23 mm

Overall length L: 68 mm

Clamp Ø D₂: 22 mm

Clamp length L₂: 22 mm

Length of brush section H₁: 25 mm

maximum speed: 18000 min⁻¹

Technical description

Clamp Ø D ₂	22 mm
maximum speed	18000 min ⁻¹
Length of brush section H ₁	25 mm
Brush Ø D ₁	23 mm
Clamp length L ₂	22 mm
Overall length L	68 mm

Type of product

End brush