

**Swarf and liquid vacuum cleaner, Manufacturer's designation: ECO-OIL13****Order data**

Order number	078559 ECO-OIL13
GTIN	5711141019312
Item class	07D

Description**Version:**

High quality, very durable Nilfisk CFM "grey line" industrial vacuum cleaner. **Swarf and liquid suction set.** With powerful smooth-running 1.3-kW turbine. Inlet Ø 50mm. Oil-proof castors with parking brakes and oil-resistant seals. Metal chips are **separated from liquids** by the swarf basket included in the scope of delivery. This allows the re-use of coolants and assists the recycling of the metal chips.

Supplied with:

Supplied with chip basket (30L), mobility trolley, drain hose. **Without accessories.**

Note:

Suitable accessories can be found under 078551-078552.

Technical description

Length	1050 mm
Height	1500 mm
Number of turbines	1
Manufacturer's designation	ECO-OIL13

Vacuum	320 mbar
Weight	120 kg
Air flow volume	46 l/s
Container volume	180 l
Width	670 mm
Operating noise	76 dB(A)
Power consumption	1300 W
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

Accessories

Industrial set Hose Ø 50 mm	078552 50
Industrial set oil-resistant Hose Ø 50 mm	078551 50