

**Garant**
**Solid carbide torus cutter R1 0.3, Diamond, Ø DC × L1: 1X6mm**

**Order data**

Order number	209726 1X6
GTIN	4045197918949
Item class	11Y

**Description**
**Version:**

With **crystalline diamond sp<sup>3</sup> coating**. For the **highest demands regarding performance and precision** in fibre-reinforced composites, CRP, GRP, and graphite. **Extremely tight tolerances** ensure maximum accuracy. Double relief ground with 2 hollow-ground chamfers. **Recess angle  $\alpha = 16^\circ$** .

Tolerances:

- **Corner radius:  $R_1 = \pm 0.0025$  mm**
- **Neck Ø:  $D_1 = 0 / -0.01$  mm**

**Note:**

At greater tool overhang lengths, use a reduced value for  $a_p$ !

Values for:

copying:  $a_p = 0.10 \times D \times a_{p, \text{korr}}$

side milling:  $a_p = 0.20 \times D \times a_{p, \text{korr}}$

**To calculate the feed rate  $vf$  please use the actual speed of the machine (the maximum possible speed)!**

e.g:  $vf = 18000$  [rpm] ×  $fz$  [mm/Z] ×  $z$

**Technical description**

Cutting edge Ø $D_c$	1 mm
Shank Ø $D_s$	4 mm
Recess Ø $D_1$	0.95 mm
Flute length $L_c$	1 mm
Feed $f_z$ for copy milling in graphite	0.03 mm
Feed $f_z$ for side milling in graphite	0.03 mm

No. of teeth Z	2
Overall length L	50 mm
Corner radius R <sub>1</sub>	0.3 mm
Overhang length L <sub>1</sub> incl. recess	6 mm
Shank	DIN 6535 HA to h5
Helix angle	30 degrees
Correction factor a <sub>p,corr</sub>	0.9
Coating	Diamond
Tool material	Solid carbide
Standard	Manufacturer's standard
Tolerance nominal Ø	0 / -0.005
Direction of infeed	horizontal, oblique and vertical
Cutting width a <sub>e</sub> for milling operation	0.5×D for side milling
Cutting width a <sub>e</sub> for milling operation	0.05×D for copy milling
Through-coolant	no
Colour ring	black
Type of product	Torus cutter

## User data

	Suitability	V <sub>c</sub>	ISO code
PVDF GF20	suitable	200 m/min	N
POM GF25	suitable	190 m/min	N
PA 66 GF30	suitable	170 m/min	N
PEEK GF30	suitable	150 m/min	N
PTFE CF25	suitable	180 m/min	N
PEEK CF30	suitable	160 m/min	N
Hybrids	suitable		
Honeycomb sandwich	suitable	350 m/min	N
GRP	suitable	190 m/min	N

GRP, CRP	suitable	190 m/min	N
Graphite	suitable	340 m/min	N
wet minimum	suitable		
dry	suitable		
Air	suitable		