

## Interior brush NOVOFLEX-B SiC120 grit, Type: 16



### Order data

Order number	574490 16
GTIN	4013349528155
Item class	57L

### Description

#### Version:

Self-centring interior brush with flexible bristles carrying **silicon carbide spheres**. Overall length 200 mm.

#### Application:

For **chamfering, finishing of surfaces** and **honing**. Generates **fine evenly ground surface** with high contact area. For use in power drills and fixed drills. Recommended speed 350 – 700 rpm, contact time 20 – 40 seconds.

#### Note:

Do not use dry, use with cutting oil No. 084205.

### Technical description

Working length $L_3$	60 mm
Brush $\varnothing D_1$	18 mm
suitable for bore $\varnothing$	14.1 - 16 mm
Shank $\varnothing D_s$	4.6 mm
Series	NOVOFLEX-B
Brush material	Silicon carbide
Grinding medium code	SiC
Grit	120
recommended speed	350 - 700 min <sup>-1</sup>
Type of product	Internal brush

---

## Accessories

High-performance cutting oil free of mineral oilUV 80  
Contents 0,25 l

084205 0,25

High-performance cutting oil free of mineral oilUV 80  
Contents 5 l

084205 5

High-performance cutting oil free of mineral oilUV 80  
Contents 20 l

084205 20