



## Torque screwdriver set, 16 pieces fully insulated, maximum torque: 300cNm



### Order data

Order number	659355 300
GTIN	4013288188335
Item class	63F

### Description

#### Version:

Kraftform handle made of impact-resistant plastic with integral soft zones facilitates torque transmission and thus protects hand and arm. Handle and blade **fully insulated up to 1000 V to DIN EN 60900 / VDE 0682-201**.

#### Content:

Slot-head blades: 0.4×2.5; 0.6×3.5; 0.8×4.0; 1.0×5.5

Blades for Phillips: PH1 and PH2

Pozidriv bits: PZ1 and PZ2

blades for Torx®: TX10; TX15; TX20; TX25

Pozidriv-slot-head combination profile: PZ/ S1 and PZ/ S2 (combination profile)

Torque screwdriver: 1 pc.

Kraftform handle for interchangeable blades: 1 pc.

### Technical description

maximum torque	300 cNm
Torque range	1.2 - 3 Nm
Torque range	120 - 300 cNm
Drive profile	Slot-head screwdriver

Drive profile	Pozidriv screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Screwdriver for TORX® screws
Drive profile	Combination profile screwdriver Pozidriv/slot-head
Measurement technology	mechanical
Torque measuring accuracy	±6 %
Test certificate	Manufacturer's test certificate
Release signalling	akustisk
Release signalling	haptisk
Direction of tightening	Right-hand tightening
Adjustable trigger value	adjustable
Connection format	exchangeable blade
Reversible reading	cNm
Data can be recorded	no
Feedback	triggering
Trigger principle	mechanical short-travel release
Setting the trigger value	with adjustment scale
Display	analogue
Measurement process	Torque
Standard	DIN EN ISO 6789
Manufacturer's designation	KK VDE 16 Torque 1.2-3.0 Nm
Type of product	Torque screwdriver

## Services

Calibration Torque screwdrivers, clockwise / anti-clockwise maximum torque 0,04-20/2 N·m

020260 0,04-20/2