

**Garant****Polishing roller (felt), Ø 100 × 100 mm, Type: SOFT****Order data**

Order number	568495 SOFT
GTIN	4045197890764
Item class	51M

**Description****Version:**

**Felt** arranged in a fan-form. Dimension **Ø 100×100 mm**, bore **Ø 19 mm** with multiple splines.

**Application:**

Large-area polishing work with enhanced flexibility and conformity to contours. Successive use of medium-hard and soft grades allows creation of a **top-class mirror finish**.

**Note:**

Felt fan-form polishing rollers must be used in conjunction **with grinding and polishing pastes** such as No. 552250 / 555740.

**Technical description**

Grinding media backing	Felt
Degree of hardness	soft
Roller Ø	100 mm
Roller width	100 mm
Product name attribute	Ø 100 × 100 mm
Bore Ø	19 mm
recommended speed	1900 min <sup>-1</sup>

Type of product

Polishing roller

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
wet maximum	suitable		

## Accessories

Polishing paste barUnipol® Colour BLUE	555740 BLUE
Polishing paste barUnipol® Colour WHITE	555740 WHITE
Grinding compound SiC Grit SiC grinding compound 280	552250 280
Grinding compound SiC Grit SiC grinding compound 150	552250 150