



Alligator® water pump pliers VDE grips, overall length: 250mm



Order data

Order number	705740 250
GTIN	4003773039303
Item class	73F

Description

Version:

Box joint (= double guidance). Designed to prevent fingers being trapped. Induction hardened. Notched serrated jaws, self-clamping on pipes and nuts. Multi-position stepped adjustment.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Pliers chrome-plated, handles insulated with multi-component covering.

Standard:

DIN ISO 8976

Material:

Chrome vanadium steel, drop forged.

Technical description

overall length	250 mm
Jaw capacity for pipes	2 in
Hexagon across flats	46 mm
Handle	Multi-component covering
Surface	chrome-plated
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 8976
Material	Chrome vanadium steel
non-sparking	no

Stepped fine adjustment	no
Self-locking	yes
Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers