

Garant**Torque wrench "Slipper" without scale, maximum torque: 1,5N·m****Order data**

Order number	657765 1,5
GTIN	4045197608895
Item class	61E

Description**Version:**

The special slipping trigger mechanism **reliably prevents unintentional overtightening**. Torque wrench **without scale**. Wrench setting using torque analyser. **Bit holder with magnet** to take 1/4 inch bits.

Handy and lightweight aluminium handle, ideal for applying small torques.

Advantage:

Precision triggering mechanism facilitates working in inaccessible places.

Function:

On reaching the set torque value the wrench triggers a clearly detectable deflection and is then immediately ready for use again. The special trigger mechanism ensures that the set torque values are reliably achieved, **but not exceeded**.

Application:

For medium to larger batch productions.

Standard:

Geprüft nach DIN EN ISO 6789.

Accuracy:

±4 % of the set value.

Cutting dataa:**Legend for drawing and formula:**

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Technical description

maximum torque	1.5 Nm
Weight	130 g
Torque measuring accuracy	±4 %
Direction of tightening	Right-hand tightening
Torque range	0.15 - 1.5 Nm
Setting the trigger value	without setting scale (requires torque analyser)
Measurement process	Torque
Adjustable trigger value	preset
Reversible reading	Nm
Trigger principle	mechanical slip clutch
Overall length L	124 mm
Feedback	triggering
Standard	DIN EN ISO 6789
Connection format	Bit holder 1/ inch
Calibration	O6
Calibration	O7
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Bit socket	D 6.3

Type of product	Torque Wrench
-----------------	---------------

Services

Calibration and adjustment Torque wrench without scale maximum torque 400 N·m	020090 400
---	------------

Adjustment Torque wrench without scale Type SET	020080 SET
--	------------

DAkkS calibration and adjustment Torque wrench without scale maximum torque 1000 N·m	020190 1000
--	-------------

Accessories

Electronic torque analyser "ProTest" maximum torque 60 N·m	654460 60
--	-----------

Torque analyser for torque wrenches "SmartCheck" maximum torque 10 N·m	654650 10
--	-----------