

**Garant**
**PickPocket end milling head, HB730, Ø D h10: 10mm**

**Order data**

Order number	210050 10
GTIN	4045197891235
Item class	21M

**Description**
**Note:**

Standard application values for  $a_{p,max} \leq 0.5 \times D$ .

**Technical description**

Head length l	13 mm
Cutter Ø D	10 mm
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.08 mm
Flute length $L_2$	7.5 mm
Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.06 mm
Arbor size	10 mm
Corner rounding $r_v$	0.32
Number of cutting edges Z	3
Series	GARANT Master Steel
Series	TopCut
Grade	HB730
Tool material	Solid carbide
Standard	Manufacturer's standard

Type	N
Spacing of the cutters	unequal spacing
Helix angle	38 degrees
Helix angle characteristic	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	0.3×D for side milling mm
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D mm
Machining strategy	HPC
Through-coolant	no
suitable arbor	GARANT TopCut
Type of product	Cutter insert for milling

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	210 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	110 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	50 m/min	H
Steel < 60 HRC	suitable only under restricted conditions	40 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	50 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	S
GG(G)	suitable	160 m/min	K

Oil	suitable only under restricted conditions
wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable only under restricted conditions
Air	suitable