


**Velour-backed abrasive disc (A) 15 holes, Ø 150 mm, Grit: 1000****Order data**

| | |
|--------------|---------------|
| Order number | 567796 1000 |
| GTIN | 4045197891365 |
| Item class | 52M |

Description**Version:**

With **stable film backing**. Dust-repellent coating prevents premature clogging.

Advantage:

- **More uniform surface finish due to outstanding grit support.**
- **Improved tear resistance when the edges are stressed.**

Application:

High-quality aluminium oxide abrasive grit (A) for general coarse, intermediate and finishing use.
High-quality aluminium oxide grit (A), open distribution. For universal applications, coarse, intermediate and finishing.

Technical description

| | |
|----------------------|--------------------------|
| Grit | 1000 |
| Disc Ø | 150 mm |
| Grinding media | Aluminium Oxide grit (A) |
| Grinding medium code | A |

| | |
|---|-----------------------------|
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 150 mm |
| Number of dust extraction holes | 15 |
| maximum circumferential speed | 40 m/s |
| Type of product | Velour-backed abrasive disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable | | |
| Uni | suitable | | |
| wet maximum | suitable | | |
| dry | suitable | | |

Accessories

567887 150

PU hook and loop backing pad Multiple holes Outer Ø 150 mm

PU hook and loop backing pad External Ø 150 mm

567885 150

Multi-hole PU backing pad External Ø 147 mm

567990 147