



Torque analyser for torque wrenches "SmartCheck", maximum torque: 400 Nm



Order data

Order number	654650 400
GTIN	4018754273027
Item class	63B

Description

Version:

Variable and flexible torque tester with rotating display and base body. Can be mounted horizontally and vertically. The display and the membrane keypad is splash-proof and the body is made of impact resistant plastic.

3 operating modes:

- **Tracking display (track)**
- **Trigger point sensing (first peak)**
- **Peak value display (peak hold)**

Units of measure: N·m, lbf·ft, lbf·in.

Advantage:

Compact and variable torque analyser. Operation on power supply or batteries.

Application:

Adjusting **torque screwdrivers and torque wrenches** with or without setting scale.

Supplied with:

With power supply unit in a sturdy plastic case.

Calibration: O4

Torque measuring accuracy: ± 1 %

Measuring range: 40 - 400 Nm

Display unit width: 120 mm

Display unit height: 124 mm
 Display unit depth: 167 mm
 Weight: 5.69 kg
 Square socket: 3/4 inch

Technical description

Measuring range	40 - 400 Nm
Display unit height	124 mm
Display unit width	120 mm
Weight	5.69 kg
Square socket	3/4 inch
maximum torque	400 Nm
Display unit depth	167 mm
Torque measuring accuracy	±1 %
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Direction of tightening	For right and left-hand tightening
Test certificate	Manufacturer's test certificate
Calibration	O4

Services

Calibration Torque analyser / sensor maximum torque 400/2 Nm	018860 400/2
DAkkS calibration Torque analyser / sensor maximum torque 1000/2 Nm	018840 1000/2