

Garant
Tap wrench, adjustable strengthened, Type: 1

Order data

Order number	148200 1
GTIN	4045197923936
Item class	11K

Description
Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **heavy** duties and **precision applications**. All dimensions with **high-quality forged steel base bodies** and integral fixed jaws. **Round vials** for straight application.

Standard: DIN 1814

Capacity □: 2 - 6.3 mm

for hand taps DIN 352: M1 – M10

for hand reamer Ø DIN 206: 2.5 - 7.5 mm

Overall length: 175 mm

Technical description

Overall length	175 mm
for hand taps DIN 352	M1 – M10
Capacity □	2 - 6.3 mm
for hand reamer Ø DIN 206	2.5 - 7.5 mm
Standard	DIN 1814
Type of product	Tap wrench