



Ergo Profi hacksaw frame 325 with bimetel blade 24 tpi



Order data

Order number	580600
GTIN	7311518214852
Item class	58Z

Description

Version:

Unique BAHCO Ergo hacksaw frame with very high blade tension (more than 1000 N/100 kP). Ergonomic design for non-fatiguing working. Very simple **spring-supported blade fastening** for quick blade change and **automatic tensioning**. Alternative blade setting at 55° for flush cutting. Overall length 400 mm.

The bow saw with its prominent bow frame is characterised by the u-shaped bow which tensions the saw blades. The limitation in depth of cut of hand bow saws is presented by the distance from the blade to the bow. This frame shape permits the use of particularly slim saw blades, which in other frame shapes would be liable to buckle when subjected to cutting movements with the force in alternate senses or other than in the pulling sense. Thanks to the thin hacksaw blades the metal cutting effort required is reduced, because of the small cutting width. Thus this type of saw is the classic standard for hacksaw work in metalworking.

Supplied with:

SANDFLEX® bimetel hacksaw blade No. 582900.

Technical description

TPI	24
Overall length	400 mm
Blade length	300 mm
Blade tension up to	1000 N
alternative saw blade angle	55 degrees

Type of product

Hacksaw frame

Accessories

Hacksaw blade, single-sidedSANDFLEX®, bimetal

582850

Hacksaw blade, single-sidedSANDFLEX®, bimetal

582920

Hacksaw blade, single-sidedSANDFLEX®, bimetal

582900