

Garant**Double ratchet ring spanner, 15° offset, Jaw widths: 14X15mm****Order data**

Order number	614845 14X15
GTIN	4045197416209
Item class	61B

Description**Version:**

Drop forged, with particularly free-running sturdy ratchet ring at each end. Reversible for left- and right-hand tightening. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

overall length L	190 mm
maximum ring height h_2	9.4 mm
Width across flats 2	15 mm
maximum ring \varnothing D2	32.6 mm
maximum ring height h_1	9.4 mm
maximum ring \varnothing D1	28.3 mm
Width across flats 1	14 mm
Width across flats	metric
No. of teeth	5
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Type of product	Spanner