

**Garant****Double ratchet ring spanner, 15° offset, Jaw widths: 8X9mm****Order data**

Order number	614845 8X9
GTIN	4045197415875
Item class	61B

**Description****Version:**

Drop forged, with particularly free-running sturdy ratchet ring at each end. Reversible for left- and right-hand tightening. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

**Technical description**

Width across flats 1	8 mm
overall length L	128 mm
maximum ring height $h_2$	7.4 mm
maximum ring height $h_1$	7.4 mm
Width across flats 2	9 mm
maximum ring $\varnothing D_2$	21.5 mm
maximum ring $\varnothing D_1$	18.2 mm
Width across flats	metric
No. of teeth	5
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Type of product	Spanner