



## “Torsiometer” torque screwdriver, maximum torque: 600cNm



### Order data

Order number	659200 600
GTIN	4018754118939
Item class	63A

### Description

#### Version:

Ergonomic handle with torsion rod measuring device.

Scale with memory pointer for right hand threads.

**Units of measurement:** cNm, lbfin

#### Application:

For controlled single tightening of screws and for controlled measurements.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

maximum torque	600 cNm
Scale graduation, 1 graduation =	20 cNm
Display	analogue
Torque measuring accuracy	±4 %
Bit socket	F 6.3
Torque range	120 - 600 cNm
Torque range	12 - 52 lbfin
Weight	230 g

Setting the trigger value	Memory pointer
Adjustable trigger value	non-adjustable
Overall length L	185 mm
Measurement process	Torque
Trigger principle	mechanical short-travel release
Standard	DIN EN ISO 6789
Feedback	displaying
Connection format	Bit holder 1/4 inch
Reversible reading	cNm
Reversible reading	lbf·in
Series	TORSIOMETER 760
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Torque fixed setting	no
Type of product	Torque screwdriver

## Services

Calibration Torque screwdrivers, clockwise / anti-clockwise  
maximum torque 0,04-20/2 N·m

020260 0,04-20/2