

Garant

Circular saw blade, metal, alternating teeth with bevel universal, Blade Ø D: 230mm

**Order data**

Order number	584095 230
GTIN	4045197220950
Item class	51S

Description**Version:**

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

Application:

For circular, cross-cut, compound, and mitre saws.

Universal circular saw blade for cutting **a wide range of materials** such as **steel flats and angle sections**, aluminium and other non-ferrous metals. Flat teeth with bevel up to Ø 250 mm; alternating set with bevel from Ø 300 mm.

Note:

Further circular saw blades can be found in Group 17.

Technical description

Blade Ø D	230 mm
Bore Ø	30 mm
Number of teeth	54

Width of cut B	2.2 mm
Type of product	Circular saw blade