



## Open ring ratchet plug-in head, Width across flats: 11 mm



### Order data

Order number	657920 11
GTIN	4035894038798
Item class	66F

### Description

#### Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Patented special head for screw fitting pipework connectors and other union nuts. With stop for screw heads; prevents slipping off.

#### Advantage:

The **ratchet function saves huge amounts of time and makes work easier** compared to conventional open ring tools.

#### Cutting dataa:

#### Legend for drawing and formula:

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

L = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

#### Suitable for:

Torque wrench with rectangular sockets.

#### Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

---

## Technical description

Width b	33 mm
Height h	11 mm
Plug-in shank	9×12 mm
Width across flats	11 mm
Pitch S	17.5 mm
Exchangeable tool	Plug-in head
Ratchet function	yes
Type of product	Ring ratchet plug-in head