

## Garant

### Double-ended ring spanner, deeply cranked, Width across flats: 30X32 mm



#### Order data

Order number	615700 30X32
GTIN	4045197160843
Item class	61A

#### Description

##### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **AS drive** profile.

##### Advantage:

**AS drive** profile:

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

##### Standard:

**DIN 838 / ISO 3318**

##### Material:

Chrome vanadium steel, chrome-plated.

##### Note:

**AS-Drive** – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. All GARANT and STAHLWILLE deep cranked double-ended ring spanners are equipped with this profile – recognisable by the **AS drive** mark.

Spanner length L: 365 mm

maximum ring  $\varnothing D_1$  max: 44 mm

maximum ring  $\varnothing D_2$  max: 48 mm

#### Technical description

maximum ring $\varnothing D_1$ max	44 mm
------------------------------------	-------

maximum ring $\varnothing D_2$ max	48 mm
Spanner length L	365 mm
Width across flats 2	32 mm
Width across flats 1	30 mm
Width across flats	metric
Type of product	Spanner