

KANON
Minimal torque gauge, maximum torque: 24cNm

Order data

Order number	658800 24
GTIN	4582126965433
Item class	66F

Description
Version:

Accurate measuring instrument for the smallest torques. Easy-to-read scale with memory pointer on the top and additional scale on the side. **With 3-jaw steel chuck.**

Application:

For measuring the smallest torques (such as rotation and frictional resistances) and for controlled tightening of screws.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Clamping chuck range	1 - 8.5 mm
maximum torque	24 cNm
Weight	600 g
Ø	63 mm
Torque range	2 - 24 cNm
Torque range	20 - 240 mNm
Release signalling	visual
Connection format	3-jaw chuck

Standard	DIN EN ISO 6789
Feedback	displaying
Setting the trigger value	Memory pointer
Series	SGK
Display	analogue
Adjustable trigger value	non-adjustable
Overall length L	132 mm
Scale graduation, 1 graduation =	0.2 cNm
Measurement process	Torque
Reversible reading	Nm
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Torque measuring accuracy	±3 %
Data can be recorded	no
Measurement technology	mechanical
Type of product	Torque Wrench

Services

CalibrationTorque wrench clockwise / anti-clockwise
maximum torque 400/2 N·m

020030 400/2