



Double-ended ring spanner, deeply cranked, phosphated, Width across flats: 16X17mm



Order data

Order number	615900 16X17
GTIN	4045197385451
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

maximum ring $\varnothing D_1$ max	25 mm
Spanner length L	263 mm
maximum ring $\varnothing D_2$ max	27 mm
Width across flats 1	16 mm
Width across flats 2	17 mm
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

