



BIT ratchet socket plug-in head, Bit-holder: 1/4in



Order data

| | |
|--------------|---------------|
| Order number | 657940 1/4 |
| GTIN | 4018754140794 |
| Item class | 63A |

Description

Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Ratchet reversible for clockwise / anticlockwise tightening.

Application:

To take bits with hexagon shank to DIN ISO 1173 C 6.3 and E 6.3 (1/4 inch).

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

The rated load on this plug-in head is limited to the corresponding jaw width, and may be less than that of the torque wrench.

Technical description

| | |
|----------------------------|---------------------------------|
| Bit-holder | 1/4 in |
| Width b | 22 mm |
| Height h | 13.6 mm |
| Plug-in shank | 9×12 mm |
| Long-term rated loading | 40 Nm |
| Exchangeable tool | Plug-in head |
| No. of teeth | 22 |
| Series | 725B |
| Pitch S | 17.5 mm |
| Material | Chrome alloy steel |
| Ratchet reversible | yes |
| Tool with ratchet function | yes |
| Type of product | BIT ratchet socket plug-in head |