

KANON
Minimal torque gauge, maximum torque: 60cNm

Order data

Order number	658800 60
GTIN	4582126965457
Item class	66F

Description
Version:

Accurate measuring instrument for the smallest torques. Easy-to-read scale with memory pointer on the top and additional scale on the side. **With 3-jaw steel chuck.**

Application:

For measuring the smallest torques (such as rotation and frictional resistances) and for controlled tightening of screws.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Clamping chuck range	1 - 8.5 mm
Ø	63 mm
Weight	600 g
maximum torque	60 cNm
Torque range	5 - 60 cNm
Torque range	50 - 600 mNm
Release signalling	visual
Connection format	3-jaw chuck

Feedback	displaying
Standard	DIN EN ISO 6789
Scale graduation, 1 graduation =	1 cNm
Setting the trigger value	Memory pointer
Measurement process	Torque
Series	SGK
Display	analogue
Adjustable trigger value	non-adjustable
Overall length L	132 mm
Reversible reading	Nm
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Torque measuring accuracy	±3 %
Data can be recorded	no
Measurement technology	mechanical
Type of product	Torque Wrench

Services

CalibrationTorque wrench clockwise / anti-clockwise maximum torque 400/2 N·m	020030 400/2
---	--------------