

**Garant**
**Torque wrench "Slipper" without scale, maximum torque: 125N·m**

**Order data**

Order number	657766 125
GTIN	4045197891679
Item class	61E

**Description**
**Version:**

The special slipping trigger mechanism **reliably prevents unintentional overtightening.**

Torque wrench **without scale.** Wrench setting using torque analyser.

With integral ratchet

**Advantage:**

Precision triggering mechanism facilitates working in inaccessible places.

**Function:**

On reaching the set torque value the wrench triggers a clearly detectable deflection and is then immediately ready for use again. The special trigger mechanism ensures that the set torque values are reliably achieved, **but not exceeded.**

**Application:**

For medium to larger batch productions.

**Standard:**

Geprüft nach DIN EN ISO 6789.

**Accuracy:**

±6 % of the set value.

**Cutting dataa:**
**Legend for drawing and formula:**

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

L = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

**Technical description**

Torque measuring accuracy	±6 %
Weight	1360 g
Torque range	40 - 125 Nm
Square drive	1/2 in
Direction of tightening	For right-hand tightening
maximum torque	125 Nm
Reversible reading	Nm
Reversible reading	lbfft
Connection format	Push-through square drive (ratchet)
Feedback	triggering
Setting the trigger value	without setting scale (requires torque analyser)
Measurement process	Torque
Overall length L	460 mm
Lever length without plug-in head [L <sub>1</sub> ]	378 mm
Trigger principle	mechanical slip clutch
Adjustable trigger value	preset
Standard	DIN EN ISO 6789
Calibration	O6
Calibration	O7
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	optisk
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque Wrench

## Services

Calibration and adjustmentTorque wrench without scale maximum torque 400 N·m	020090 400
AdjustmentTorque wrench without scale Type SET	020080 SET
DAkkS calibrationTorque wrench maximum torque 1000 N·m	020020 1000
DAkkS calibration and adjustmentTorque wrench without scale maximum torque 1000 N·m	020190 1000

### Accessories

Electronic torque analyser“ProTest” maximum torque 400 N·m	654460 400
Electronic torque analyser“ProTest” maximum torque 60 N·m	654460 60