

**HOLEX**

## Double-ended ring spanner set, deeply cranked, phosphated, Number of keys: 8



### Order data

Order number	615910 8
GTIN	4045197385611
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.

**HOLEX** – With oval shaft.

**Standard:**

**DIN 838 / ISO 3318**

**Material:**

**HOLEX** – Chrome vanadium steel, phosphated.

**Supplied with:**

1 each double ended ring spanner No. 615600 / 615000 / 615900 / 615950: 6x7; 8x9; 10x11; 12x13; 14x15; 16x17; 18x21; 19x22

### Technical description

Number of keys	8
Width across flats	metric
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	phosphated

Product name attribute	phosphated
Type of product	Spanner

---

## Accessories

Double-ended ring spanner, deeply cranked Width across flats 18X21 mm	615900 18X21
Double-ended ring spanner, deeply cranked Width across flats 12X13 mm	615900 12X13
Double-ended ring spanner, deeply cranked Width across flats 10X11 mm	615900 10X11
Double-ended ring spanner, deeply cranked Width across flats 14X15 mm	615900 14X15
Double-ended ring spanner, deeply cranked Width across flats 16X17 mm	615900 16X17
Double-ended ring spanner, deeply cranked Width across flats 8X9 mm	615900 8X9
Double-ended ring spanner, deeply cranked Width across flats 6X7 mm	615900 6X7
Double-ended ring spanner, deeply cranked Width across flats 19X22 mm	615900 19X22