



“Torsiometer” torque screwdriver, maximum torque: 75cNm



Order data

Order number	659200 75
GTIN	4018754118908
Item class	63A

Description

Version:

Ergonomic handle with torsion rod measuring device.

Scale with memory pointer for right hand threads.

Units of measurement: cNm, lbfin

Application:

For controlled single tightening of screws and for controlled measurements.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Display	analogue
maximum torque	75 cNm
Scale graduation, 1 graduation =	2.5 cNm
Torque measuring accuracy	±4 %
Bit socket	F 6.3
Torque range	15 - 75 cNm
Torque range	1.5 - 6.5 lbfin
Adjustable trigger value	non-adjustable

Feedback	displaying
Overall length L	185 mm
Setting the trigger value	Memory pointer
Trigger principle	mechanical short-travel release
Reversible reading	cNm
Reversible reading	lbf·in
Weight	225 g
Measurement process	Torque
Standard	DIN EN ISO 6789
Connection format	Bit holder 1/4 inch
Series	TORSIOMETER 760
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Torque fixed setting	no
Type of product	Torque screwdriver

Services

Calibration Torque screwdrivers, clockwise / anti-clockwise
maximum torque 0,04-20/2 N·m

020260 0,04-20/2