



## HSS jobber drill N, uncoated, Ø DC h8: 23mm



### Order data

Order number	116320 23
GTIN	4045197029706
Item class	12C

### Description

#### Version:

Special surface treatment, resulting in reduced tendency to edge build-up **and improved chip evacuation.**

#### Recommendation:

#### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530.**

### Technical description

Number of cutting edges Z	2
Nominal Ø D <sub>c</sub>	23 mm
Flute length L <sub>c</sub>	155 mm
Feed f in steel < 750 N/mm <sup>2</sup>	0.2 mm/rev.
Tolerance nominal Ø	h8
Overall length L	253 mm
Morse taper MT size	2
Standard	DIN 345
recommended maximum drilling depth L <sub>2</sub>	120.5 mm
Point angle	118 degrees
Shank	Morse taper

Coating	uncoated
Tool material	HSS
Type	N
Helix angle	20-30 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Oil	suitable		
wet maximum	suitable		