



## LED work lamp, Type: 2



### Order data

Order number	081415 2
GTIN	4260131238086
Item class	08C

### Description

#### Version:

Powerful, dimmable, long-lived and robust work lamps with **flexible neck** and **sturdy magnetic base**. For connection to a 24 V mains adapter or 24 V machine control system. High-performance LED in an aluminium casing, cold white approx. 5500 Kelvin. Spot beam for focussed light.

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Supplied with 250-V power supply unit.

#### Note:

Suitable table clamps and magnetic holders can be found under 081418/081419.

### Technical description

Weight	760 g
Power supply	Mains-powered
IP Index of Protection	IP 65

Bulb	LED
Type of fastening	Magnetic Base
Illumination	200 lm
Magnetic base Ø	66 mm
Light output	2 W
Nominal voltage	250 V
Colour temperature	5500 K
ATEX zone	no
Overall height	600 mm
Light colour	cold white
Lamp head Ø	28 mm
Type of product	Desk lamp / workstation lamp

---

## Accessories

Table clamp Top mounting plate Ø 95 mm	081418 95
Magnetic holder Top mounting plate Ø 95 mm	081419 95