

Garant**Roller cabinet with 6 drawers, Number of drawers: 6****Order data**

Order number	914510 6
GTIN	4045197892072
Item class	9GT

Description**Version:**

The stable sheet metal housing of the mobile workbench is fitted with perforated side panels for storage of accessories. Inner faces of drawers have slots for dividers. The drawers are unlocked by a catch incorporated in the grip handle. Drawers are centrally lockable by means of a **cylinder lock**. With roller bearing wheels (2 castors with parking brake, 2 fixed wheels).

Steel tray with X-ABS inlay.

Solid ergonomic handle of glass fibre-reinforced PP.

Fitted with:

Drawer front height: 60; 60; 120; 120; 120; 180 mm

Supplied with:

Dividing material. 4 divider plates for a 60 mm drawer, 3 divider plates for a 120 mm drawer.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Technical description

Weight	45 kg
Width	660 mm

Drawer usable depth	300 mm
Number of drawers	6
Height	950 mm
Depth	380 mm
Drawer usable width	500 mm
Drawer/pull-out shelf load capacity	30 kg
Drawer runner extension (partial/full extension)	75 %
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular lock barrel
Type of product	Roller cabinet

Accessories

Barrel sleeve 225-010-43 without lock barrel	914208
--	--------