

**Erdi****Ideal snips with 2-component handles, right-hand cutting, overall length: 260mm**

## Order data

Order number	765900 260
GTIN	4010220030226
Item class	73X

## Description

### Version:

Drop-forged head, blades induction hardened. Adjustable pivot pins, double leverage with integrated return spring.

Snip jaws made of **stainless steel** (HRC 60 – 62) with optimised, non-serrated blade geometry for high manoeuvrability and easy cutting using up to **25 % less force**, ideal for cutting decorative sheets. Handles of sheet metal, nickel-plated. 2-component handle with non-slip insert of soft material, easy on the hand.

**Cutting capacity:** Sheet metal up to 1.8 mm, stainless steel up to 1.2 mm.

### Application:

For continuous straight and shaped cutting.

## Technical description

overall length	260 mm
Length cutter	33 mm
Application type	right-hand cutting
Type of product	Scissors

## Accessories

Repair kit for Ideal snips

766020