



Torque screwdrivers with digital display, to take interchangeable blades, maximum torque: 250cNm



Order data

Order number	659911 250
GTIN	7610733249626
Item class	63D

Description

Version:

Power grip with comfortable easy-grip Haptoprene surface allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

The desired torque for sizes 80, 250 and 500 is set using a 3 AF hexagon screwdriver, and 4 AF for size 1600. The torque setting is displayed in a window (**digital display at the end of the handle**). Activation of the digital display by pressing with a finger (pressure sensor). The automatic cut-out after approx. 20 seconds enables a battery life of more than 10 years. The battery can be changed at the factory or during recalibration. Display changeover between Nm and lbf. ft.

To take **interchangeable blades** (8 mm No. 659870 – 659884 and 6 mm No. 659920 – 659928).

Application:

For controlled tightening of screws to a pre-set torque.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

maximum torque	250 cNm
suitable interchangeable blades	6 mm

Data sheet

Ø	35 mm
Display	digital
Resolution	2 cNm
Torque measuring accuracy	±6 %
Torque range	40 - 250 cNm
Torque range	0.4 - 2.5 Nm
#Article no of the battery / rechargeable battery fitted	CR1225
#Number of batteries contained	1
Adjustable trigger value	adjustable
Connection format	exchangeable blade
Overall length L	122 mm
Setting the trigger value	preset
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Type of product	Torque screwdriver

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/659911-250>