



Double-ended ring spanner, straight, Width across flats: 10X11 mm



Order data

| | |
|--------------|---------------|
| Order number | 617600 10X11 |
| GTIN | 4018754021253 |
| Item class | 63A |

Description

Version:

Drop-forged. With close tolerance jaw widths.

STAHLWILLE – With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Thin, flat rings for use in restricted places. With **AS-Drive** profile.

Standard:

DIN 837 B / ISO 3318

Material:

STAHLWILLE – Chrome alloy steel; non-flaking chrome-plated over nickel; smoothed finish surface.

Technical description

| | |
|-------------------------------------|-----------------------------|
| Width across flats 1 | 10 mm |
| maximum ring height $h_{1 \max}$ | 6 mm |
| Width across flats 2 | 11 mm |
| maximum ring $\varnothing D_2 \max$ | 17 mm |
| Spanner length L | 130 mm |
| maximum ring $\varnothing D_1 \max$ | 16 mm |
| Width across flats | metric |
| Ring setting | 0 degrees |
| Manufacturing process | drop forged |
| Material | Chrome alloy steel |
| Surface | chrome-plated (non-flaking) |

Type of product

Spanner