



## Torque screwdriver TorqueVario®, maximum torque: 100cNm



### Order data

Order number	659930 100
GTIN	4010995264611
Item class	63K

### Description

#### Version:

Numerical display of the torque value via scale in the window (40 – 50 individual values, depending on the torque range). Torque continuously adjustable using Torque-Setter (included). On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then immediately ready for use again. Accuracy class  $\pm 6\%$ .

#### Application:

For checking threaded fastenings to the specified torque, in combination with a Wiha Torque interchangeable bit No. 659932 – 659946.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Setting standard for size 60-700: No. 659931 size1 and for size 1400: No. 659931 size 2.

### Technical description

maximum torque	100 cNm
Ø	23 mm
Display	analogue
Torque measuring accuracy	$\pm 6\%$
Torque range	40 - 100 cNm
Torque range	0.4 - 1 Nm

Overall length L	127 mm
Standard	DIN EN ISO 6789
Measurement process	Torque
Trigger principle	mechanical short-travel release
Adjustable trigger value	preset
Reversible reading	Nm
Setting the trigger value	with adjustment scale
Feedback	triggering
Connection format	exchangeable blade
Weight	147 g
Series	TorqueVario®
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Scale graduation, 1 graduation =	0.05 Nm
Manufacturer's designation	TorqueVario®-S
Torque fixed setting	no
Type of product	Torque screwdriver

## Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------

## Accessories

Adjustment tool Torque Setter Type 1	659931 1
--------------------------------------	----------

