



Double-ended ring spanner, shallow cranked, Width across flats: 20X22mm



Order data

| | |
|--------------|---------------|
| Order number | 616500 20X22 |
| GTIN | 4018754021802 |
| Item class | 63A |

Description

Version:

Drop-forged. With close tolerance jaw widths. Thin, flat rings for use in restricted places. With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Shallow cranked head at each end. With **AS-Drive** profile.

Standard:

DIN 897 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Technical description

| | |
|--|-----------------------------|
| Spanner length L | 280 mm |
| maximum ring $\varnothing D_1$ max | 28.5 mm |
| maximum ring height $h_{1\text{ max}}$ | 14.5 mm |
| maximum ring $\varnothing D_2$ max | 31.3 mm |
| Width across flats 2 | 22 mm |
| Width across flats 1 | 20 mm |
| Width across flats | metric |
| Manufacturing process | drop forged |
| Material | Chrome alloy steel |
| Surface | chromium-plated over nickel |
| Type of product | Spanner |

