



Double-ended ring spanner, straight, phosphated, Width across flats: 24X27 mm



Order data

Order number	617900 24X27
GTIN	4045197385789
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.

HOLEX – With oval shaft.

Standard:

DIN 837 B / ISO 3318

Material:

HOLEX – Chrome vanadium steel, phosphated.

Spanner length L: 258 mm

maximum ring $\varnothing D_1$ max: 35 mm

maximum ring $\varnothing D_2$ max: 38.5 mm

maximum ring height $h_{1\max}$: 11 mm

Technical description

Width across flats 1	24 mm
Width across flats 2	27 mm
maximum ring $\varnothing D_2$ max	38.5 mm
maximum ring height $h_{1\max}$	11 mm
maximum ring $\varnothing D_1$ max	35 mm
Spanner length L	258 mm
Width across flats	metric
Ring setting	0 degrees

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner